










Dekkramme Gira E2 med tekstfelt antrasitt



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	1091 23	1/10		4010337084044
 Dobbel vannrett	1092 23	1/10		4010337084099
 Dobbel lodrett	1102 23	1/10		4010337089148
 3-dobbel vannrett	1093 23	1/5		4010337084174
 3-dobbel vertikal	1103 23	1/5		4010337084211
 4-dobbel vannrett	1094 23	1/5		4010337084259
 4-dobbel loddrett	1114 23	1/5		4010337084297
 5-dobbel vannrett	1095 23	1/5		4010337084372
 5-dobbel loddrett	1115 23	1/5		4010337084334

Egenskaper

- Bruddsikker.
 - Sprøytetåketett.
 - Dekkramme med transparent vindu for merking av innsatsene.
 - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
 - Plast: halogenfri, slag- og bruddsikker termoplast, eller heter det da polykarbonat.
-

Merknader

- Må ikke brukes sammen med: tetningssett IP44, påvegghus av flat konstruksjon, påvegghus.
-