










## Høytaler innfelt radio IP



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvit glans	2282 01	1		4010337076230
 renhvit glans	2282 03 6306546	1		4010337076247
 renhvit silkematt	2282 27	1		4010337076254
 antrasitt	2282 28	1		4010337076261
 aluminiumsfarget	2282 26	1		4010337076162
 svart matt	2282 005	1		4010337037286
 grå matt	2282 015	1		4010337083931
 rustfritt stål	2282 600	1		4010337032861

## Egenskaper

- Høytaler for tilkobling til Gira innfelt radio.

---

## Tekniske data

Monteringsdybde:	32 mm
Tilkoblingstverrsnitt - Høytaler-/AUX-tilkobling:	1,5 mm <sup>2</sup>
Impedans:	8 Ω
Omgivelsestemperatur:	-5 °C til +50 °C

---