







Dobbel SCHUKO-stikkontakt 16 A 250 V~ med økt berøringsbeskyttelse (Safety Plus) for innfelt apparatboks enkel



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvit glans	2731 01	-	-	4010337881100
 renhvit glans	2731 03 1522564	-	-	4010337881117
 renhvit silkematt	2731 27 1522567	-	-	4010337881124
 antrasitt	2731 28 1522568	-	-	4010337000778
 aluminiumsfarget	2731 26 1522566	-	-	4010337000761
 svart matt	2731 005 1522902	-	-	4010337037538

Tekniske data

Monteringsdybde:	25 mm
Tilkoblingstverrsnitt - For ledninger fra:	1,5 mm ² til 2,5 mm ²
Omgivelsestemperatur - økt berøringsbeskyttelse:	0 °C til +45 °C
Byggehøyde:	17,5 mm

Merknader

- Passer i alle standard 60 mm koblingsbokser.
 - Økt berøringsbeskyttelse (Safety Plus) i henhold til DIN VDE 0620-1.
-