







Dobbel SCHUKO-stikkontakt 16 A 250 V~ med økt berøringsbeskyttelse (Safety Plus) for innfelt apparatboks, 1,5-dobbel



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvit glans	2735 01	-	-	4010337000822
 renhvit glans	2735 03 1522575	-	-	4010337771371
 renhvit silkematt	2735 27 1522573	-	-	4010337771555
 antrasitt	2735 28 1522574	-	-	4010337771364
 aluminiumsfarget	2735 26 1522572	-	-	4010337000785
 svart matt	2735 005 1522903	-	-	4010337037521

#### Tekniske data

Monteringsdybde:	25 mm
Tilkoblingstverrsnitt - For ledninger fra:	1,5 mm <sup>2</sup> til 2,5 mm <sup>2</sup>
Byggehøyde:	6 mm

## **Merknader**

- Passer til kompakbokser Attema UK 40 og type H 140 fra ABB/HAF.
  - Økt berøringsbeskyttelse (Safety Plus) i henhold til DIN VDE 0620-1.
-