


Stikkontakt britisk standard (BS 1363), 13 A 250 V~ med shutter System 55



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvit glans	2776 01	-	-	4010337079347
 renhvit glans	2776 03	-	-	4010337079354
 antrasitt	2776 28	-	-	4010337079378
 aluminiumsfarget (lakkert)	2776 26	-	-	4010337079361
 svart matt (lakkert)	2776 005	-	-	4010337037774
 grå matt (lakkert)	2776 015	-	-	4010337086352
 rustfritt stål (lakkert)	2776 600	-	-	4010337022077

Egenskaper

- Med skruklemmer.

Tekniske data

Monteringsdybde: 17 mm

Merknader

- Kun for skruefeste.
 - Ytterligere funksjoner og varianter kan fås på forespørsel også for 80-utførelsen av BS-kontakten.
-