

## Stikkontakt britisk standard (BS 1363), 13 A 250 V~ koblet, med shutter System 55



| Spesifikasjon                                                                                                  | Bestillings nr. | PE | PS | EAN           |
|----------------------------------------------------------------------------------------------------------------|-----------------|----|----|---------------|
|  kremhvit glans               | 2778 01         | -  | -  | 4010337079477 |
|  renhvit glans              | 2778 03         | -  | -  | 4010337079484 |
|  antrasitt                  | 2778 28         | -  | -  | 4010337079507 |
|  aluminiumsfarget (lakkert) | 2778 26         | -  | -  | 4010337079491 |
|  svart matt (lakkert)       | 2778 005        | -  | -  | 4010337037750 |
|  grå matt (lakkert)         | 2778 015        | -  | -  | 4010337086390 |
|  rustfritt stål (lakkert)   | 2778 600        | -  | -  | 4010337022091 |

### Egenskaper

- Med skruklemmer.

## Tekniske data

Monteringsdybde: 20 mm

---

## Merknader

- Kun for skruefeste.
  - Ytterligere funksjoner og varianter kan fås på forespørsel også for 80-utførelsen av BS-kontakten.
-