


Stikkontakt britisk standard (BS 1363), 13 A 250 V~ koblet, med shutter System 55



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvit glans	2778 01	-	-	4010337079477
 renhvit glans	2778 03	-	-	4010337079484
 antrasitt	2778 28	-	-	4010337079507
 aluminiumsfarget (lakkert)	2778 26	-	-	4010337079491
 svart matt (lakkert)	2778 005	-	-	4010337037750
 grå matt (lakkert)	2778 015	-	-	4010337086390
 rustfritt stål (lakkert)	2778 600	-	-	4010337022091

Egenskaper

- Med skruklemmer.

Tekniske data

Monteringsdybde: 20 mm

Merknader

- Kun for skruefeste.
 - Ytterligere funksjoner og varianter kan fås på forespørsel også for 80-utførelsen av BS-kontakten.
-