








Universal-utkoblingsvendebryter



| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|--|-----------------|----|----|---------------|
|  kremhvit glans | 2832 01 | - | - | 4010337832010 |
|  renhvit glans | 2832 03 | - | - | 4010337832034 |
|  antrasitt | 2832 28 | - | - | 4010337832287 |
|  aluminiumsfarget | 2832 26 | - | - | 4010337832263 |
|  svart matt | 2832 005 | - | - | 4010337038528 |
|  grå matt | 2832 015 | - | - | 4010337087120 |
|  rustfritt stål (lakkert) | 2832 600 | - | - | 4010337022053 |

Tekniske data

Monteringsdybde: 25 mm

Tilkoblingstverrsnitt
- For ledninger inntil: 2,5 mm²

Merknader

- Kun for skruefeste.
