








## Universal-utkoblingsvendebryter



| Spesifikasjon  | Bestillings nr. | PE | PS | EAN           |
|--|-----------------|----|----|---------------|
|  kremhvit glans             | 2832 01         | -  | -  | 4010337832010 |
|  renhvit glans            | 2832 03         | -  | -  | 4010337832034 |
|  antrasitt                | 2832 28         | -  | -  | 4010337832287 |
|  aluminiumsfarget         | 2832 26         | -  | -  | 4010337832263 |
|  svart matt               | 2832 005        | -  | -  | 4010337038528 |
|  grå matt                 | 2832 015        | -  | -  | 4010337087120 |
|  rustfritt stål (lakkert) | 2832 600        | -  | -  | 4010337022053 |

### Tekniske data

Monteringsdybde: 25 mm

Tilkoblingstverrsnitt  
- For ledninger inntil: 2,5 mm<sup>2</sup>

## **Merknader**

- Kun for skruefeste.

---