

Vippekontrollbryter british standard (BS EN 60669-1) 20 AX 250 V~med vippe og kontrolllys Utkoblingsbryter 2-polet



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvit glans	2834 01	-	-	4010337078814
 renhvit glans	2834 03	-	-	4010337078821
 antrasitt	2834 28	-	-	4010337078845
 aluminiumsfarget	2834 26	-	-	4010337078838
 svart matt	2834 005	-	-	4010337038573
 grå matt	2834 015	-	-	4010337087137
 rustfritt stål	2834 600	-	-	4010337022305

Tekniske data

Monteringsdybde:	24 mm
Tilkoblingstverrsnitt - For ledninger inntil:	2 x 4 mm ² eller 1 x 6 mm ²

Merknader

- Kun for skruefeste.
 - BS EN 60669-1.
-