

Vippekontrollbryter british standard (BS EN 60669-1) 20 AX 250 V~med vippe og kontrolllys Utkoblingsbryter 2-polet



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvit glans	2834 01	-	-	4010337078814
 renhvit glans	2834 03	-	-	4010337078821
 antrasitt	2834 28	-	-	4010337078845
 aluminiumsfarget (lakkert)	2834 26	-	-	4010337078838
 svart matt (lakkert)	2834 005	-	-	4010337038573
 grå matt (lakkert)	2834 015	-	-	4010337087137
 rustfritt stål	2834 600	-	-	4010337022305

Tekniske data

Monteringsdybde: 24 mm

Tilkoblingstverrsnitt
- For ledninger inntil: 2 x 4 mm² eller 1 x 6 mm²

Merknader

- Kun for skruefeste.
 - BS EN 60669-1.
-