








Vippekontrollbryter british standard (BS EN 60669-1) 20 AX 250 V~med vippe og kontrolllys Utkoblingsbryter 2-polet

| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|--|-----------------|----|----|---------------|
|  kremhvit glans | 2834 01 | - | - | 4010337078814 |
|  renhvit glans | 2834 03 | - | - | 4010337078821 |
|  antrasitt | 2834 28 | - | - | 4010337078845 |
|  aluminiumsfarget | 2834 26 | - | - | 4010337078838 |
|  svart matt | 2834 005 | - | - | 4010337038573 |
|  grå matt | 2834 015 | - | - | 4010337087137 |
|  rustfritt stål | 2834 600 | - | - | 4010337022305 |

Tekniske data

Monteringsdybde: 24 mm

Tilkoblingstverrsnitt
- For ledninger inntil: 2 x 4 mm² eller 1 x 6 mm²

Merknader

- Kun for skruefeste.
 - BS EN 60669-1.
-