








## Stikkontakt med beskyttelseskontakt EURO-US 16 A 250 V~

Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvit glans	2840 01	-	-	4010337840015
 renhvit glans	2840 03	-	-	4010337840039
 renhvit silkematt	2840 27	-	-	4010337840275
 antrasitt	2840 28	-	-	4010337840282
 aluminiumsfarget	2840 26	-	-	4010337840268
svart matt	2840 005	-	-	4010337037873
 grå matt	2840 015	-	-	4010337087151
 rustfritt stål (lakkert)	2840 600	-	-	4010337022213

### Tekniske data

Monteringsdybde: 20 mm