








## Vippetrykknapp 3-dobbel 10 A 250 V~med vipper Lukkekontakt 1-polet



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvit glans	2844 01	-	-	4010337082033
 renhvit glans	2844 03	-	-	4010337082040
 antrasitt	2844 28	-	-	4010337082064
 aluminiumsfarget	2844 26	-	-	4010337082057
 svart matt	2844 005	-	-	4010337037903
 grå matt	2844 015	-	-	4010337087182
 rustfritt stål (lakkert)	2844 600	-	-	4010337021957

### Tekniske data

Monteringsdybde: 25 mm

Tilkoblingstverrsnitt  
- For ledninger inntil: 2,5 mm<sup>2</sup>

## **Merknader**

- Kun for skruefeste.

---