










Vippe med kontrollvindu



| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|---|-----------------|----------|----|---------------|
|  kremhvit glans | 3290 01 | 1 | | 4010337041610 |
|  renhvit glans | 3290 03 | 1/10/100 | | 4010337041627 |
|  renhvit silkematt | 3290 27 | 1/10/100 | | 4010337041641 |
|  antrasitt | 3290 28 | 1/10/100 | | 4010337041658 |
|  aluminiumsfarget | 3290 26 | 1 | | 4010337041634 |
|  svart matt | 3290 005 | 1/10 | | 4010337067047 |
|  grå matt | 3290 015 | 1/10 | | 4010337110491 |
|  rustfritt stål | 3290 600 | 1/5 | | 4010337045403 |