

## Vippe



| Spesifikasjon                                                                                                  | Bestillings nr. | PE       | PS | EAN           |
|----------------------------------------------------------------------------------------------------------------|-----------------|----------|----|---------------|
|  kremhvit glans               | 3296 01         | 1/10     |    | 4010337039341 |
|  renhvit glans              | 3296 03         | 1/10/100 |    | 4010337039358 |
|  renhvit silkematt          | 3296 27         | 1/10/100 |    | 4010337039372 |
|  antrasitt                  | 3296 28         | 1/10/100 |    | 4010337039389 |
|  aluminiumsfarget (lakkert) | 3296 26         | 1/10     |    | 4010337039365 |
|  svart matt (lakkert)       | 3296 005        | 1/10     |    | 4010337065593 |
|  grå matt (lakkert)         | 3296 015        | 1/10     |    | 4010337110521 |
|  rustfritt stål             | 3296 600        | 1/10     |    | 4010337043867 |