

## Bæring Modular Jack dobbel Bæring MJ-01 til MJ-10



| Spesifikasjon                                                                                    | Bestillings nr.    | PE   | PS | EAN           |
|--------------------------------------------------------------------------------------------------|--------------------|------|----|---------------|
|  Bæring MJ-01   | 5601 00<br>6944031 | 1/10 |    | 4010337460015 |
|  Bæring MJ-02 | 5602 00<br>6944032 | 1/10 |    | 4010337460022 |
|  Bæring MJ-03 | 5603 00            | 1/10 |    | 4010337460039 |
|  Bæring MJ-04 | 5604 00<br>6944034 | 1/10 |    | 4010337460046 |
|  Bæring MJ-05 | 5605 00<br>6944035 | 1/10 |    | 4010337460053 |
|  Bæring MJ-06 | 5606 00<br>6944036 | 1/10 |    | 4010337460060 |
|  Bæring MJ-07 | 5607 00<br>6944037 | 1/10 |    | 4010337460077 |
|  Bæring MJ-08 | 5608 00<br>6944038 | 1/10 |    | 4010337460084 |
|  Bæring MJ-09 | 5609 00<br>6944039 | 1/10 |    | 4010337460091 |



Bæring MJ-10

5610 00  
6944040

1/10

4010337460107

---

## Tekniske data

### Mål

|                       |                    |
|-----------------------|--------------------|
| - MJ-01, MJ02, MJ-07: | B 14,8 x 19,5 mm   |
| - MJ-03:              | B 14,8 x H 20,0 mm |
| - MJ-04, MJ-09:       | B 14,8 x 19,3 mm   |
| - MJ-05:              | B 16,7 x H 17,3 mm |
| - MJ-06:              | B 15,9 x H 18,3 mm |
| - MJ-08:              | B 14,8 x H 19,0 mm |
| - MJ-10:              | B 16,1 x H 18,5 mm |

---

## Merknader

- Kun for skruefeste.
  - Egnet for kanalinstallasjon.
-