

Pierścień nośny Modular Jack 2x Element montażowy MJ-01 do MJ-10



Specyfikacja	Nr katalogowy	Jednostka opakowania	SC	EAN
 Pierścień nośny MJ-01	5601 00	1/10		4010337460015
 Pierścień nośny MJ-02	5602 00	1/10		4010337460022
 Pierścień nośny MJ-03	5603 00	1/10		4010337460039
 Pierścień nośny MJ-04	5604 00	1/10		4010337460046
 Pierścień nośny MJ-05	5605 00	1/10		4010337460053
 Pierścień nośny MJ-06	5606 00	1/10		4010337460060
 Pierścień nośny MJ-07	5607 00	1/10		4010337460077
 Pierścień nośny MJ-08	5608 00	1/10		4010337460084
 Pierścień nośny MJ-09	5609 00	1/10		4010337460091



Pierścień nośny MJ-10

5610 00

1/10

4010337460107

Dane techniczne

Wymiary

- MJ-01, MJ02, MJ-07:	szer. 14,8 × 19,5 mm
- MJ-03:	szer. 14,8 × wys. 20,0 mm
- MJ-04, MJ-09:	B 14,8 x 19,3 mm
- MJ-05:	szer. 16,7 × wys. 17,3 mm
- MJ-06:	B 15,9 x H 18,3 mm
- MJ-08:	szer. 14,8 × wys. 19,0 mm
- MJ-10:	szer. 16,1 × wys. 18,5 mm

Wskazówki

- Tylko do mocowania śrubowego.
 - Nadaje się do instalacji kanałowej.
-