

Pierścień nośny Modular Jack 2x Element montażowy MJ-01 do MJ-10



Specyfikacja	Nr katalogowy	Jednostka opakowania	SC	EAN
 Pierścień nośny MJ-01	5601 00	1/10	01	4010337460015
 Pierścień nośny MJ-02	5602 00	1/10	01	4010337460022
 Pierścień nośny MJ-03	5603 00	1/10	01	4010337460039
 Pierścień nośny MJ-04	5604 00	1/10	01	4010337460046
 Pierścień nośny MJ-05	5605 00	1/10	01	4010337460053
 Pierścień nośny MJ-06	5606 00	1/10	01	4010337460060
 Pierścień nośny MJ-07	5607 00	1/10	01	4010337460077
 Pierścień nośny MJ-08	5608 00	1/10	01	4010337460084
 Pierścień nośny MJ-09	5609 00	1/10	01	4010337460091



Pierścień nośny MJ-10

5610 00

1/10

01

4010337460107

Dane techniczne

Wymiary

- | | |
|-----------------------|---------------------------|
| - MJ-01, MJ02, MJ-07: | szer. 14,8 × 19,5 mm |
| - MJ-03: | szer. 14,8 × wys. 20,0 mm |
| - MJ-04, MJ-09: | B 14,8 x 19,3 mm |
| - MJ-05: | szer. 16,7 × wys. 17,3 mm |
| - MJ-06: | Wymiary |
| - MJ-08: | szer. 14,8 × wys. 19,0 mm |
| - MJ-10: | szer. 16,1 × wys. 18,5 mm |

Wskazówki

- Tylko do mocowania śrubowego.
 - Nadaje się do instalacji kanałowej.
-