








Täckram Gira Standard 55 kritvit blank



Specifikation	Artikelnr.	FE	PS	EAN
 1knapp	0211 03 1854080	1/10/100		4010337211037
 1,5knappars	1001 03 1850125	1/10		4010337881308
 2knappars	0212 03 1854081	1/10/100		4010337212034
 2fack utan mellanbalk	1002 03 1854085	1/10		4010337001607
 3-knappars	0213 03 1854082	1/10/100		4010337213031
 4knappars	0214 03 1854083	1/5		4010337214038
 5knappars	0215 03 1854084	1/5		4010337215035

Egenskaper

- Plast: halogenfri, slag- och brottsäker termoplast, eller kallas det då polykarbonat.

Hänvisningar

- Även avsedd för kanalinstallation.
 - Täckram (1- till 5-fack) i kombination med tätningssats även lämplig för kapslad infälld IP44 installation.
-