








Täckram Gira E2 svart matt



| Specifikation | Artikelnr. | FE | PS | EAN |
|---|--------------------|------|----|---------------|
|  1knapp | 0211 09 1860369 | 1/10 | | 4010337036739 |
|  1,5knappars | 1001 09 1850403 | 1/10 | | 4010337072775 |
|  2knappars | 0212 09 1850367 | 1/10 | | 4010337036760 |
|  2fack utan mellanbalk | 1002 09 1850372 | 1/10 | | 4010337036784 |
|  3-knappars | 0213 09 1850368 | 1/5 | | 4010337036821 |
|  4knappars | 0214 09 1850369 | 1/5 | | 4010337036869 |
|  5knappars | 0215 09 1850370 | 1/5 | | 4010337036906 |

Egenskaper

- Plast: halogenfri, slag- och brottsäker termoplast, eller kallas det då polykarbonat.

Hänvisningar

- Även avsedd för kanalinstallation.
 - Täckram (1- till 5-fack) i kombination med tätningssats även lämplig för kapslad infälld IP44 installation.
-