








Täckram Gira E2 antracit



Specifikation	Artikelnr.	FE	PS	EAN
 1knapp	0211 23 1852008	1/10/100		4010337211235
 1,5knappars	1001 23 1850132	1/10		4010337881339
 2knappars	0212 23 1852012	1/10/100		4010337212232
 2fack utan mellanbalk	1002 23 1852013	1/10		4010337002239
 3-knappars	0213 23 1852016	1/5		4010337213239
 4knappars	0214 23 1852020	1/5		4010337214236
 5knappars	0215 23 1852024	1/5		4010337215233

Egenskaper

- Plast: halogenfri, slag- och brottsäker termoplast, eller kallas det då polykarbonat.

Hänvisningar

- Även avsedd för kanalinstallation.
 - Täckram (1- till 5-fack) i kombination med tätningssats även lämplig för kapslad infälld IP44 installation.
-