








Täckram Gira E2 alufärg



Specifikation	Artikelnr.	FE	PS	EAN
 1knapp	0211 25 1852006	1/10/100		4010337211259
 1,5knappars	1001 25 1850129	1/10		4010337881346
 2knappars	0212 25 1852010	1/10		4010337212256
 2fack utan mellanbalk	1002 25 1852017	1/10		4010337002253
 3-knappars	0213 25 1852014	1/5		4010337213253
 4knappars	0214 25 1852018	1/5		4010337214250
 5knappars	0215 25 1852022	1/5		4010337215257

Egenskaper

- Plast: halogenfri, slag- och brottsäker termoplast, eller kallas det då polykarbonat.

Hänvisningar

- Även avsedd för kanalinstallation.
 - Täckram (1- till 5-fack) i kombination med tätningssats även lämplig för kapslad infälld IP44 installation.
-