

## Täckram Gira E2 grå matt (lackerad)



| Specifikation                                                                                             | Artikelnr.         | FE   | PS | EAN           |
|-----------------------------------------------------------------------------------------------------------|--------------------|------|----|---------------|
|  1knapp                  | 0211 37<br>1850425 | 1/10 |    | 4010337077299 |
|  1,5knappars           | 1001 37            | 1/10 |    | 4010337082422 |
|  2knappars             | 0212 37<br>1850427 | 1/10 |    | 4010337077589 |
|  2fack utan mellanbalk | 1002 37            | 1/10 |    | 4010337082439 |
|  3-knappars            | 0213 37<br>1850428 | 1/5  |    | 4010337077602 |
|  4knappars             | 0214 37<br>1850429 | 1/5  |    | 4010337077626 |
|  5knappars             | 0215 37<br>1850430 | 1/5  |    | 4010337077640 |

## Egenskaper

- Plast: halogenfri, slag- och brottsäker termoplast, eller kallas det då polykarbonat.

## Hänvisningar

- Även avsedd för kanalinstallation.
  - Täckram (1- till 5-fack) i kombination med tätningssats även lämplig för kapslad infälld IP44 installation.
-