







Täckram Gira F200 antracit (lackerad)



| Specifikation | Artikelnr. | FE | PS | EAN |
|---|------------|------|----|---------------|
|  1knapp | 0211 73 | 1/10 | | 4010337113157 |
|  2knappars | 0212 73 | 1/10 | | 4010337113201 |
|  2fack utan mellanbalk | 1002 73 | 1/10 | | 4010337113416 |
|  3-knappars | 0213 73 | 1/5 | | 4010337113256 |
|  4knappars | 0214 73 | 1/5 | | 4010337113317 |
|  5knappars | 0215 73 | 1/5 | | 4010337113362 |

Egenskaper

- I färgvarianten renvit glansig: tillverkad av 85 % biobaserad plast.

Tekniska data

| | |
|-------------------|---------------------------|
| Täckram 1kn: | B 90,0 x H 90,0 x T 11,4 |
| Täckram 2kn: | B 90,0 x H 161,1 x T 11,4 |
| Täckram 5kn u/MB: | B 90,0 x H 161,1 x T 11,4 |

| | |
|--|---------------------------|
| Täckram 3kn: | B 90,0 x H 232,6 x T 11,4 |
| Täckram 4kn: | B 90,0 x H 303,9 x T 11,4 |
| Täckram 5kn: | B 90,0 x H 375,2 x T 11,4 |
| Hörnradie: | R 0,3 |
| Biocirkulär plast - Färgvariant: kritvit blank: | min. 50% |
