

Täckram Gira F300 kritvit sidenmatt (lackerad)



Specifikation	Artikelnr.	FE	PS	EAN
 1knapp	0211 82	1/10		4010337113485
 2knappars	0212 82	1/10		4010337113546
 2fack utan mellanbalk	1002 82	1/10		4010337131854
 3-knappars	0213 82	1/5		4010337113591
 4knappars	0214 82	1/5		4010337113645
 5knappars	0215 82	1/5		4010337131847

Tekniska data

Täckram 1kn:	B 80,8 x H 80,8 x T 11,4
Täckram 2kn:	B 80,8 x H 151,9 x T 11,4
Täckram 5kn u/MB:	B 80,8 x H 151,9 x T 11,4
Täckram 3kn:	B 80,8 x H 223,4 x T 11,4
Täckram 4kn:	B 80,8 x H 297,7 x T 11,4
Täckram 5kn:	B 80,8 x H 366,0 x T 11,4
Hörnradie:	R 0,5

