







Täckram Gira F300 svart matt (lackerad)



| Specifikation | Artikelnr. | FE | PS | EAN |
|---|------------|------|----|---------------|
|  1knapp | 0211 84 | 1/10 | | 4010337113508 |
|  2knappars | 0212 84 | 1/10 | | 4010337113553 |
|  2fack utan mellanbalk | 1002 84 | 1/10 | | 4010337131892 |
|  3-knappars | 0213 84 | 1/5 | | 4010337113607 |
|  4knappars | 0214 84 | 1/5 | | 4010337113652 |
|  5knappars | 0215 84 | 1/5 | | 4010337131885 |

Egenskaper

- I färgvarianten renvit glansig: tillverkad av 85 % biobaserad plast.

Tekniska data

| | |
|-------------------|---------------------------|
| Täckram 1kn: | B 80,8 x H 80,8 x T 11,4 |
| Täckram 2kn: | B 80,8 x H 151,9 x T 11,4 |
| Täckram 5kn u/MB: | B 80,8 x H 151,9 x T 11,4 |

| | |
|--|---------------------------|
| Täckram 3kn: | B 80,8 x H 223,4 x T 11,4 |
| Täckram 4kn: | B 80,8 x H 297,7 x T 11,4 |
| Täckram 5kn: | B 80,8 x H 366,0 x T 11,4 |
| Hörnradie: | R 0,5 |
| Biocirkulär plast - Färgvariant: kritvit blank: | min. 50% |
