







Täckram Gira F300 grå matt (lackerad)



Specifikation	Artikelnr.	FE	PS	EAN
 1knapp	0211 86	1/10		4010337113492
 2knappars	0212 86	1/10		4010337113522
 2fack utan mellanbalk	1002 86	1/10		4010337131915
 3-knappars	0213 86	1/5		4010337113577
 4knappars	0214 86	1/5		4010337113621
 5knappars	0215 86	1/5		4010337131908

Egenskaper

- I färgvarianten renvit glansig: tillverkad av 85 % biobaserad plast.

Tekniska data

Täckram 1kn:	B 80,8 x H 80,8 x T 11,4
Täckram 2kn:	B 80,8 x H 151,9 x T 11,4
Täckram 5kn u/MB:	B 80,8 x H 151,9 x T 11,4

Täckram 3kn:	B 80,8 x H 223,4 x T 11,4
Täckram 4kn:	B 80,8 x H 297,7 x T 11,4
Täckram 5kn:	B 80,8 x H 366,0 x T 11,4
Hörnradie:	R 0,5
Biocirkulär plast - Färgvariant: kritvit blank:	min. 50%
