








Täckram Gira E2 svart matt



Specifikation	Artikelnr.	FE	PS	EAN
 1knapp	0211 09 1860369	1/10		4010337036739
 1,5knappars	1001 09 1850403	1/10		4010337072775
 2knappars	0212 09 1850367	1/10		4010337036760
 2fack utan mellanbalk	1002 09 1850372	1/10		4010337036784
 3-knappars	0213 09 1850368	1/5		4010337036821
 4knappars	0214 09 1850369	1/5		4010337036869
 5knappars	0215 09 1850370	1/5		4010337036906

Egenskaper

- Plast: halogenfri, slag- och brottsäker termoplast, eller kallas det då polykarbonat.

Hänvisningar

- Även avsedd för kanalinstallation.
 - Täckram (1- till 5-fack) i kombination med tätningssats även lämplig för kapslad infälld IP44 installation.
-