







Täckram Gira F300 svart matt (lackerad)



Specifikation	Artikelnr.	FE	PS	EAN
 1knapp	0211 84	1/10		4010337113508
 2knappars	0212 84	1/10		4010337113553
 2fack utan mellanbalk	1002 84	1/10		4010337131892
 3-knappars	0213 84	1/5		4010337113607
 4knappars	0214 84	1/5		4010337113652
 5knappars	0215 84	1/5		4010337131885

Egenskaper

- I färgvarianten renvit glansig: tillverkad av 85 % biobaserad plast.

Tekniska data

Täckram 1kn:	B 80,8 x H 80,8 x T 11,4
Täckram 2kn:	B 80,8 x H 151,9 x T 11,4
Täckram 5kn u/MB:	B 80,8 x H 151,9 x T 11,4

Täckram 3kn:	B 80,8 x H 223,4 x T 11,4
Täckram 4kn:	B 80,8 x H 297,7 x T 11,4
Täckram 5kn:	B 80,8 x H 366,0 x T 11,4
Hörnradie:	R 0,5
Biocirkulär plast - Färgvariant: kritvit blank:	min. 50%
