








Täckram Gira Standard 55 kritvit sidenmatt



Specifikation	Artikelnr.	FE	PS	EAN
 1knapp	0211 04 1852000	1/10/100		4010337211044
 1,5knappars	1001 04 1850127	1/10		4010337881315
 2knappars	0212 04 1852001	1/10/100		4010337212041
 2fack utan mellanbalk	1002 04 1852002	1/10		4010337002048
 3-knappars	0213 04 1852003	1/10/100		4010337213048
 4knappars	0214 04 1852004	1/5		4010337214045
 5knappars	0215 04 1852005	1/5		4010337215042

Egenskaper

- Plast: halogenfri, slag- och brottsäker termoplast, eller kallas det då polykarbonat.

Hänvisningar

- Även avsedd för kanalinstallation.
 - Täckram (1- till 5-fack) i kombination med tätningssats även lämplig för kapslad infälld IP44 installation.
-