







## Täckram Gira E2



| Specifikation                                                                                             | Artikelnr.         | FE   | PS | EAN           |
|-----------------------------------------------------------------------------------------------------------|--------------------|------|----|---------------|
|  1knapp                  | 0211 33<br>1850315 | 1/10 |    | 4010337019794 |
|  2knappars             | 0212 33<br>1850327 | 1/10 |    | 4010337019800 |
|  2fack utan mellanbalk | 1002 33            | 1/10 |    | 4010337019848 |
|  3-knappars            | 0213 33<br>1850334 | 1/5  |    | 4010337019817 |
|  4knappars             | 0214 33<br>1850340 | 1/5  |    | 4010337019824 |
|  5knappars             | 0215 33<br>1850342 | 1/5  |    | 4010337019831 |

## Hänvisningar

- Även avsedd för kanalinstallation.
- Täckram (1- till 5-fack) i kombination med tätningssats även lämplig för kapslad infälld IP44 installation.