







## Täckram Gira F200 antracit (lackerad)



Specifikation	Artikelnr.	FE	PS	EAN
 1knapp	0211 73	1/10		4010337113157
 2knappars	0212 73	1/10		4010337113201
 2fack utan mellanbalk	1002 73	1/10		4010337113416
 3-knappars	0213 73	1/5		4010337113256
 4knappars	0214 73	1/5		4010337113317
 5knappars	0215 73	1/5		4010337113362

### Egenskaper

- I färgvarianten renvit glansig: tillverkad av 85 % biobaserad plast.

### Tekniska data

Täckram 1kn:	B 90,0 x H 90,0 x T 11,4
Täckram 2kn:	B 90,0 x H 161,1 x T 11,4
Täckram 5kn u/MB:	B 90,0 x H 161,1 x T 11,4

Täckram 3kn:	B 90,0 x H 232,6 x T 11,4
Täckram 4kn:	B 90,0 x H 303,9 x T 11,4
Täckram 5kn:	B 90,0 x H 375,2 x T 11,4
Hörnradie:	R 0,3
Biocirkulär plast - Färgvariant: kritvit blank:	min. 50%

---