





Täckram Gira F200 för platt montering antracit (lackerad)



| Specifikation | Artikelnr. | FE | PS | EAN |
|--|------------|------|----|---------------|
|  1knapp | 0211 735 | 1/10 | | 4010337108887 |
|  2knappars | 0212 735 | 1/10 | | 4010337108962 |
|  3-knappars | 0213 735 | 1/5 | | 4010337109297 |
|  4knappars | 0214 735 | 1/5 | | 4010337109341 |

Egenskaper

- I färgvarianten renvit glansig: tillverkad av 85 % biobaserad plast.

Tekniska data

| | |
|--|--------------------------|
| Täckram 1kn: | B 90,0 x H 90,0 x T 3,4 |
| Täckram 2kn: | B 90,0 x H 161,1 x T 3,4 |
| Täckram 3kn: | B 90,0 x H 232,6 x T 3,4 |
| Täckram 4kn: | B 90,0 x H 303,9 x T 3,4 |
| Hörradie: | R 0,3 |
| Biocirkulär plast - Färgvariant: kritvit blank: | min. 50% |