








Täckram Gira Standard 55 cremevit blank



Specifikation	Artikelnr.	FE	PS	EAN
 1knapp	0211 01	1/10/100		4010337211013
 1,5knappars	1001 01	1/10		4010337881247
 2knappars	0212 01	1/10/100		4010337212010
 2fack utan mellanbalk	1002 01	1/10		4010337002017
 3-knappars	0213 01	1/10/100		4010337213017
 4knappars	0214 01	1/5		4010337214014
 5knappars	0215 01	1/5		4010337215011

Egenskaper

- Plast: halogenfri, slag- och brottsäker termoplast, eller kallas det då polykarbonat.

Hänvisningar

- Även avsedd för kanalinstallation.
 - Täckram (1- till 5-fack) i kombination med tätningssats även lämplig för kapslad infälld IP44 installation.
-