







Täckram Gira F100 kritvit sidenmatt (lackerad)



Specifikation	Artikelnr.	FE	PS	EAN
 1knapp	0211 172	1/10		4010337133506
 2knappars	0212 172	1/10		4010337133513
 2fack utan mellanbalk	1002 172	1/10		4010337133551
 3-knappars	0213 172	1/5		4010337133520
 4knappars	0214 172	1/5		4010337133537
 5knappars	0215 172	1/5		4010337133544

Egenskaper

- I färgvarianten renvit glansig: tillverkad av 85 % biobaserad plast.

Tekniska data

Täckram 1kn:	B 83,3 x H 83,3 x T 10,6
Täckram 2kn:	B 83,3 x H 154,4 x T 10,6
Täckram 5kn u/MB:	B 83,3 x H 154,4 x T 10,6

Täckram 3kn:	B 83,3 x H 225,9 x T 10,6
Täckram 4kn:	B 83,3 x H 297,2 x T 10,6
Täckram 5kn:	B 83,3 x H 368,5 x T 10,6
Hörnradie:	R 3
Biocirkulär plast - Färgvariant: kritvit blank:	min. 50%
