







## Täckram Gira F100 antracit (lackerad)



| Specifikation   | Artikelnr. | FE   | PS | EAN           |
|---|------------|------|----|---------------|
|  1knapp                  | 0211 173   | 1/10 |    | 4010337135951 |
|  2knappars             | 0212 173   | 1/10 |    | 4010337133568 |
|  2fack utan mellanbalk | 1002 173   | 1/10 |    | 4010337133605 |
|  3-knappars            | 0213 173   | 1/5  |    | 4010337133575 |
|  4knappars             | 0214 173   | 1/5  |    | 4010337133582 |
|  5knappars             | 0215 173   | 1/5  |    | 4010337133599 |

### Egenskaper

- I färgvarianten renvit glansig: tillverkad av 85 % biobaserad plast.

### Tekniska data

|                   |                           |
|-------------------|---------------------------|
| Täckram 1kn:      | B 83,3 x H 83,3 x T 10,6  |
| Täckram 2kn:      | B 83,3 x H 154,4 x T 10,6 |
| Täckram 5kn u/MB: | B 83,3 x H 154,4 x T 10,6 |

|  |                           |
|--|---------------------------|
| Täckram 3kn:                                       | B 83,3 x H 225,9 x T 10,6 |
| Täckram 4kn:                                       | B 83,3 x H 297,2 x T 10,6 |
| Täckram 5kn:                                       | B 83,3 x H 368,5 x T 10,6 |
| Hörnradie:   | R 3                       |
| Biocirkulär plast<br>- Färgvariant: kritvit blank: | min. 50%                  |

---