

Täckram Gira F100 svart matt (lackerad)



Specifikation	Artikelnr.	FE	PS	EAN
 1knapp	0211 174	1/10		4010337135968
 2knappars	0212 174	1/10		4010337133612
 2fack utan mellanbalk	1002 174	1/10		4010337133650
 3-knappars	0213 174	1/5		4010337133629
 4knappars	0214 174	1/5		4010337133636
 5knappars	0215 174	1/5		4010337135845

Tekniska data

Täckram 1kn:	B 83,3 x H 83,3 x T 10,6
Täckram 2kn:	B 83,3 x H 154,4 x T 10,6
Täckram 5kn u/MB:	B 83,3 x H 154,4 x T 10,6
Täckram 3kn:	B 83,3 x H 225,9 x T 10,6
Täckram 4kn:	B 83,3 x H 297,2 x T 10,6
Täckram 5kn:	B 83,3 x H 368,5 x T 10,6
Hörnradie:	R 3

