








Täckram Gira E2 kritvit blank



Specifikation	Artikelnr.	FE	PS	EAN
 1knapp	0211 29 1852025	1/10/100		4010337211297
 1,5knappars	1001 29 1850128	1/10		4010337881353
 2knappars	0212 29 1852026	1/10/100		4010337212294
 2fack utan mellanbalk	1002 29 1852021	1/10		4010337001553
 3-knappars	0213 29 1852027	1/5		4010337213291
 4knappars	0214 29 1852028	1/5		4010337214298
 5knappars	0215 29 1852029	1/5		4010337215295

Egenskaper

- Plast: halogenfri, slag- och brottsäker termoplast, eller kallas det då polykarbonat.

Hänvisningar

- Även avsedd för kanalinstallation.
 - Täckram (1- till 5-fack) i kombination med tätningssats även lämplig för kapslad infälld IP44 installation.
-