

Täckram Gira E2 grå matt (lackerad)



Specifikation	Artikelnr.	FE	PS	EAN
 1knapp	0211 37 1850425	1/10		4010337077299
 1,5knappars	1001 37	1/10		4010337082422
 2knappars	0212 37 1850427	1/10		4010337077589
 2fack utan mellanbalk	1002 37	1/10		4010337082439
 3-knappars	0213 37 1850428	1/5		4010337077602
 4knappars	0214 37 1850429	1/5		4010337077626
 5knappars	0215 37 1850430	1/5		4010337077640

Egenskaper

- Plast: halogenfri, slag- och brottsäker termoplast, eller kallas det då polykarbonat.

Hänvisningar

- Även avsedd för kanalinstallation.
 - Täckram (1- till 5-fack) i kombination med tätningssats även lämplig för kapslad infälld IP44 installation.
-