







Täckram Gira F100 antracit (lackerad)



| Specifikation | Artikelnr. | FE | PS | EAN |
|---|------------|------|----|---------------|
|  1knapp | 0211 173 | 1/10 | | 4010337135951 |
|  2knappars | 0212 173 | 1/10 | | 4010337133568 |
|  2fack utan mellanbalk | 1002 173 | 1/10 | | 4010337133605 |
|  3-knappars | 0213 173 | 1/5 | | 4010337133575 |
|  4knappars | 0214 173 | 1/5 | | 4010337133582 |
|  5knappars | 0215 173 | 1/5 | | 4010337133599 |

Egenskaper

- I färgvarianten renvit glansig: tillverkad av 85 % biobaserad plast.

Tekniska data

| | |
|-------------------|---------------------------|
| Täckram 1kn: | B 83,3 x H 83,3 x T 10,6 |
| Täckram 2kn: | B 83,3 x H 154,4 x T 10,6 |
| Täckram 5kn u/MB: | B 83,3 x H 154,4 x T 10,6 |

| | |
|--|---------------------------|
| Täckram 3kn: | B 83,3 x H 225,9 x T 10,6 |
| Täckram 4kn: | B 83,3 x H 297,2 x T 10,6 |
| Täckram 5kn: | B 83,3 x H 368,5 x T 10,6 |
| Hörnradie: | R 3 |
| Biocirkulär plast - Färgvariant: kritvit blank: | min. 50% |
