








Täckram Gira E2 kritvit sidenmatt



Specifikation	Artikelnr.	FE	PS	EAN
 1knapp	0211 22 1852007	1/10/100		4010337211228
 1,5knappars	1001 22 1850130	1/10		4010337881322
 2knappars	0212 22 1852011	1/10/100		4010337212225
 2fack utan mellanbalk	1002 22 1852009	1/10		4010337002222
 3-knappars	0213 22 1852015	1/5		4010337213222
 4knappars	0214 22 1852019	1/5		4010337214229
 5knappars	0215 22 1852023	1/5		4010337215226

Egenskaper

- Plast: halogenfri, slag- och brottsäker termoplast, eller kallas det då polykarbonat.

Hänvisningar

- Även avsedd för kanalinstallation.
 - Täckram (1- till 5-fack) i kombination med tätningssats även lämplig för kapslad infälld IP44 installation.
-