










Stary - Vippa



Specifikation	Artikelnr.	FE	PS	EAN
 cremevit blank	0296 01	-	-	4010337296010
 kritvit blank	0296 03 1854001	-	-	4010337296034
 kritvit sidenmatt	0296 27 1851801	-	-	4010337296270
 antracit	0296 28 1851802	-	-	4010337296287
 alufärg	0296 26 1851800	-	-	4010337296263
 svart matt	0296 005 1850399	-	-	4010337038061
 grå matt	0296 015 1850409	-	-	4010337080220
 rostfritt stål	0296 600 1850393	-	-	4010337021667

Hänvisningar

- Täckram (1- till 5fack) ur strömställarprogrammet Standard 55 och Gira E2 passar i kombination med tätningssatsen även för kapslad installation, vattenskyddad enligt IP44, av vippbrytare och vipptryckknappar (gäller ej för vippta 2-knappars).
 - Beroende på tillgänglighet.
-