







## Täckram Gira F100 kritvit blank



Specifikation	Artikelnr.	FE	PS	EAN
 1knapp	0211 112 1852191	1/10		4010337043973
 2knappars	0212 112 1852192	1/10		4010337044017
 2fack utan mellanbalk	1002 112	1/10		4010337047094
 3-knappars	0213 112 1852193	1/5		4010337044031
 4knappars	0214 112 1852194	1/5		4010337044055
 5knappars	0215 112 1852195	1/5		4010337044079

### Egenskaper

- Slagtålig.
- I färgvarianten renvit glansig: tillverkad av 85 % biobaserad plast.

### Tekniska data

Täckram 1kn:	B 83,3 x H 83,3 x T 10,6
Täckram 2kn:	B 83,3 x H 154,4 x T 10,6
Täckram 5kn u/MB:	B 83,3 x H 154,4 x T 10,6

Täckram 3kn:	B 83,3 x H 225,9 x T 10,6
Täckram 4kn:	B 83,3 x H 297,2 x T 10,6
Täckram 5kn:	B 83,3 x H 368,5 x T 10,6
Hörnradie:	R 3
Biocirkulär plast	
- Färgvariant: kritvit blank:	min. 50%

---

## Hänvisningar

- I kombination med tätningsslans även lämplig för kapslad infälld montering enligt IP44.

---