







## Täckram Gira F300 antracit (lackerad)



Specifikation	Artikelnr.	FE	PS	EAN
 1knapp	0211 83	1/10		4010337113461
 2knappars	0212 83	1/10		4010337113515
 2fack utan mellanbalk	1002 83	1/10		4010337131878
 3-knappars	0213 83	1/5		4010337113560
 4knappars	0214 83	1/5		4010337113614
 5knappars	0215 83	1/5		4010337131861

### Egenskaper

- I färgvarianten renvit glansig: tillverkad av 85 % biobaserad plast.

### Tekniska data

Täckram 1kn:	B 80,8 x H 80,8 x T 11,4
Täckram 2kn:	B 80,8 x H 151,9 x T 11,4
Täckram 5kn u/MB:	B 80,8 x H 151,9 x T 11,4

Täckram 3kn:	B 80,8 x H 223,4 x T 11,4
Täckram 4kn:	B 80,8 x H 297,7 x T 11,4
Täckram 5kn:	B 80,8 x H 366,0 x T 11,4
Hörnradie:	R 0,5
Biocirkulär plast - Färgvariant: kritvit blank:	min. 50%

---