


## Högtalare inbyggd radio IP



| Specifikation                                                                                             | Artikelnr.         | FE | PS | EAN           |
|-----------------------------------------------------------------------------------------------------------|--------------------|----|----|---------------|
|  cremevit blank          | 2282 01            | 1  |    | 4010337076230 |
|  kritvit blank         | 2282 03<br>6240068 | 1  |    | 4010337076247 |
|  kritvit sidenmatt     | 2282 27<br>6240070 | 1  |    | 4010337076254 |
|  antracit              | 2282 28<br>6240071 | 1  |    | 4010337076261 |
|  alufärg (lackerad)    | 2282 26<br>6240069 | 1  |    | 4010337076162 |
|  svart matt (lackerad) | 2282 005           | 1  |    | 4010337037286 |
|  grå matt (lackerad)   | 2282 015           | 1  |    | 4010337083931 |
|  rostfritt stål        | 2282 600           | 1  |    | 4010337032861 |
|  svart glas-design     | 2282 05<br>6240260 | 1  |    | 4010337889182 |

## Egenskaper

- Högtalare för anslutning till Gira inbyggd radio.

---

## Tekniska data

|                                                |                     |
|------------------------------------------------|---------------------|
| Inbyggnadsdjup:                                | 32 mm               |
| Anslutningsarea<br>- Högtalar-/AUX-anslutning: | 1,5 mm <sup>2</sup> |
| impedans:                                      | 8 Ω                 |
| Omgivningstemperatur:                          | -5 °C till +50 °C   |

---