

## Universal-av-trapp



| Specifikation                                                                                                 | Artikelnr.          | FE   | PS | EAN           |
|---------------------------------------------------------------------------------------------------------------|---------------------|------|----|---------------|
|  cremevit blank              | 2832 01             | -    | -  | 4010337832010 |
|  kritvit blank             | 2832 03<br>1850000  | -    | -  | 4010337832034 |
|  antracit                  | 2832 28<br>1850002  | 1/10 |    | 4010337832287 |
|  alufärg (lackerad)        | 2832 26<br>1850001  | 1/10 |    | 4010337832263 |
|  svart matt (lackerad)     | 2832 005<br>1850406 | -    | -  | 4010337038528 |
|  grå matt (lackerad)       | 2832 015<br>1850414 | -    | -  | 4010337087120 |
|  rostfritt stål (lackerat) | 2832 600            | -    | -  | 4010337022053 |

### Tekniska data

Inbyggnadsdjup: 25 mm

Anslutningsarea  
- för ledare till: 2,5 mm<sup>2</sup>

## Hänvisningar

- Endast för skruvfastsättning.

---