

Universal-av-trapp



Specifikation	Artikelnr.	FE	PS	EAN
 cremevit blank	2832 01	-	-	4010337832010
 kritvit blank	2832 03 1850000	-	-	4010337832034
 antracit	2832 28 1850002	1/10		4010337832287
 alufärg (lackerad)	2832 26 1850001	1/10		4010337832263
 svart matt (lackerad)	2832 005 1850406	-	-	4010337038528
 grå matt (lackerad)	2832 015 1850414	-	-	4010337087120
 rostfritt stål (lackerat)	2832 600	-	-	4010337022053

Tekniska data

Inbyggnadsdjup: 25 mm

Anslutningsarea
- för ledare till: 2,5 mm²

Hänvisningar

- Endast för skruvfastsättning.
