








Universal-av-trapp



| Specifikation | Artikelnr. | FE | PS | EAN |
|---|---------------------|------|----|---------------|
|  cremevit blank | 2832 01 | - | - | 4010337832010 |
|  kritvit blank | 2832 03 1850000 | - | - | 4010337832034 |
|  antracit | 2832 28 1850002 | 1/10 | - | 4010337832287 |
|  alufärg | 2832 26 1850001 | 1/10 | - | 4010337832263 |
|  svart matt | 2832 005 1850406 | - | - | 4010337038528 |
|  grå matt | 2832 015 1850414 | - | - | 4010337087120 |
|  rostfritt stål (lackerat) | 2832 600 | - | - | 4010337022053 |

Tekniska data

| | |
|---------------------------------------|---------------------|
| Inbyggnadsdjup: | 25 mm |
| Anslutningsarea - för ledare till: | 2,5 mm ² |

Hänvisningar

- Endast för skruvfastsättning.
