








Vipptryckknapp 3-knappars 10 A 250 V~med vippor Slutande kontakt 1-polig



Specifikation	Artikelnr.	FE	PS	EAN
 cremevit blank	2844 01	1/10		4010337082033
 kritvit blank	2844 03 1850005	1/10		4010337082040
 antracit	2844 28 1850007	1/10		4010337082064
 alufärg	2844 26 1850006	1/10		4010337082057
 svart matt	2844 005	-	-	4010337037903
 grå matt	2844 015	1/10		4010337087182
 rostfritt stål (lackerat)	2844 600	-	-	4010337021957

Tekniska data

Inbyggnadsdjup:	25 mm
Anslutningsarea - för ledare till:	2,5 mm ²

Hänvisningar

- Endast för skruvfastsättning.
